



**NOTES:**

COORDINATE SETUP AND INSTALLATION WITH UNIVERSITY'S REPRESENTATIVE

**PERFORMANCE DATE:**

SIZE	LOWEST FLOW WITHIN ±5% ACCURACY	LOWEST FLOW WITHIN ±2% ACCURACY	NOMINAL FLOW WITHIN ±2% ACCURACY	MAXIMUM FLOW WITHIN ±2% ACCURACY
1 1/2"	1.8 GPM	4.4 GPM	44 GPM	55 GPM
2"	5.3 GPM	20 GPM	66 GPM	95 GPM
3"	14 GPM	53 GPM	176 GPM	220 GPM
4"	21 GPM	79 GPM	264 GPM	380 GPM
6"	53 GPM	198 GPM	660 GPM	860 GPM
8"	97 GPM	357 GPM	1189 GPM	1500 GPM

**CV VALUES**

SIZE	Cv (FLOW RATE AT 1.0 PSI OF HEADLOSS)
1 1/2"	23 GPM
2"	35 GPM
3"	92 GPM
4"	139 GPM
6"	347 GPM
8"	624 GPM